# Help for choosing the TRIO AC UPS

## Select your TRIO AC UPS with integrated energy storage here.

| | TRIO UPS, 1~ | |
|---|---|---|
| | | |
| Input | 96 V AC … 138 V AC | 184 V AC … 264 V AC |
| W x H x D in mm | 210 x 170 x 136 | 210 x 170 x 136 |

| | 120 V / 750 VA | 230 V / 750 VA |
|---|---|---|
| Type | TRIO-UPS-2G/1AC/1AC/120V/750VA | TRIO-UPS-2G/1AC/1AC/230V/750VA |
| Item number | 2905908 | 2905909 |
| Information | Energy storage device with lead AGM technology | Energy storage device with lead AGM technology |

### Buffer times for TRIO AC UPS:

1+1: An additional energy storage device of the same capacity (4 Ah) of type UPS-BAT/PB/24DC/4AH (1274117) is required in this case.

| Perfor-mance | Buffer time | | | | | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|---|---|---|---|---|
| | Minutes | | | | | | | | | | | | Hours | |
| | 1 | 1.5 | 2 | 4 | 6 | 8 | 10 | 15 | 20 | 30 | 40 | 50 | 1 | 1.5 |
| 50 W | | | | | | | | | | | | 1+1 | 1+1 | 1+1 |
| 100 W | | | | | | | | | | 1+1 | 1+1 | 1+1 | | |
| 150 W | | | | | | | | 1+1 | 1+1 | 1+1 | | | | |
| 200 W | | | | | | | 1+1 | 1+1 | 1+1 | | | | | |
| 250 W | | | | | | 1+1 | 1+1 | 1+1 | | | | | | |
| 300 W | | | | | 1+1 | 1+1 | 1+1 | | | | | | | |
| 400 W | | | | 1+1 | 1+1 | 1+1 | | | | | | | | |
| 500 W | | | 1+1 | 1+1 | 1+1 | | | | | | | | | |
| 600 W | | 1+1 | 1+1 | 1+1 | | | | | | | | | | |

The data is based on an ambient temperature of +20°C.